

ACTIVE 1D®

SIMPLE, RELIABLE, AND AUTONOMOUS

Principle and operating

The Active 1D[®] excitation advance is obtained by a device named «impulse device». Its principle consists in storing electrostatic energy present in the atmosphere at a stormy cloud approach to release the ascending discharge excitation in a good time.

This device operates with an integrated sensor which measures the surrounding electrical field value.

It generates then a polarity inversion of the lightning rod head, creating a sudden amplification of the electrical field on its point.

Active ID® characteristics

- Taking into account the energy character to choose the leader which has the capacity to transform into an ascending tracer,
- · Autonomous and clean energy source : atmospheric electrical field,
- · Cloud polarity taken into account,
- Optimized head bending radius to reduce the corona effect and guarantee the excitation advance,
- · Guarantee of functioning in all weather conditions,
- High resistance to corrosion,
- In compliance with NFC 17-102 standard of September 2011.

Active 1D® protection radius

The Active 1D[®] has been tested in laboratory according to NFC 17-102 standard protocol.

These tests showed, according to models, excitation advances from 12 µs to 60µs regarding to a simple rod.




FRANKIN ACTIVE 1D® RANGE

Enhanced protection zone

The Active 1D^{\circ} radii of protection here below mentioned, are defined for the four Np levels of protection (from 1 to IV) regarding to h real height between the lightning rod point and the highest point of the structure to protect.

- ΔT : Excitation advance, for Active 1D[®], ΔT =12, 25, 45 and 60µs
- Np : level of protection with more or less severity (I to IV) determined by the lightning risk assessment with the Lightning Risk software according to NFC 17-102 standard,
- h(m): height between the lightning rod point and the highest point of the structure to protect.



Active 1D®		AFB10	0121D			AFB1	0251D			AFB1	0451D			AFB1	0601D	
Np h(m)	1	Ш	Ш	IV	1	Ш	Ш	IV	1	Ш	Ш	IV	1	П	Ш	IV
2	11	13	16	19	17	20	23	26	25	28	32	36	31	34	39	43
4	23	27	32	37	34	39	46	52	51	57	65	72	63	69	78	85
5	28	34	41	46	42	49	57	65	63	71	81	89	79	86	97	107
6	29	34	42	48	43	49	58	66	63	71	81	90	79	87	97	107
8	30	36	43	50	43	50	59	67	64	72	82	91	79	87	98	108
10	30	37	45	52	44	51	61	69	64	72	83	92	79	88	99	109
20	32	41	51	60	45	54	65	73	65	74	86	97	80	89	102	113
30	32	42	55	65	45	55	68	80	65	75	89	101	80	90	104	116

Active ID® range

Model	∆T(µs)	Lightning counter	Model	∆T(µs)	Lightning counter
AFB10121D	12	Not included	AFB10251D	25	Not included
AFB17121D	12	Included	AFB17251D	25	Included
Model	∆T(µs)	Lightning counter	Model	∆T(µs)	Lightning counter
Model AFB10451D	ΔT(μs) 45	Lightning counter	Model AFB10601D	ΔT(μs) 60	Lightning counter

Active ID® test

The Active 1D[®] can be tested on site with AFV0050TT wire test case (initial check, periodical checks according to NFC 17-102 standard and decrees in force, maintenance,...);

Simple and fast, this test can be done either disassembling the lightning rod, either using the AFV0087PT test perch, to check lightning rods at a height of 8 meters without dismantling.

This tester power supply operates with a battery (provided). The display with indicator lights indicates instantly the obtained result (positive or negative)

Packing

Complete lightning rod packed in reinforced cardboard box

- Weight : 3,00 Kg
- Dimensions : 430 x 110 x 110 mm



FRANKLIN FRANCE - 13, Rue Louis Armand - 77330 OZOIR-LA-FERRIERE (France) Tél : +33 1 60 34 54 44 - Fax +33 1 64 40 35 43 www.franklin-france.com





BR001EN.QLF.00

in